



HIRSCHMANN

A BELDEN BRAND

Product information STAKWI 3 grau/grey

Industrial Connecting Solutions:Rectangular Connectors:Power Connectors (ST series):Cable socket:STAKWI 3 grau/grey

<https://catalog.beldensolutions.com:443/link/57078-24228-256261-24351-24352-35783/en/conf/uistate>

Name	STAKWI 3 grau/grey
	Angled cable socket
Delivery informations	
Availability	available
Product description	
Description	Angled cable socket
Type	STAKWI 3 grau/grey
Order No.	932 413-106
Type of contact	female
Number of contacts	3 + PE
Cable gland	PG 11
Cable diameter	6 mm to 10 mm
Conductor size	max. 1.5 mm ²
Housing Color	grey
Contact bearer color	black
Technical data	
Pin dimensions	2 mm
Rated voltage	AC 400 V / DC 250 V
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
Type of termination	screw
Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	
Housing	UL 94 HB
Contact bearer	UL 94 V-0
Approvals	
UL	UL
VDE	VDE
SEV	SEV
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 3, order no. 732 045-001



HIRSCHMANN


A Belden Brand

Industrial Connecting Solutions: Rectangular Connectors: Power Connectors (ST series): Cable socket: STAKWI 3 grau/grey

<https://catalog.beldensolutions.com:443/link/57078-24228-256261-24351-24352-35783/en/conf/ui/state>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.