

BPSD00050432101M00

Search by : Part Number Characteristics Cross reference



MP

Unshielded Type


Series Pdf

RoHSREACHCoC

Product detail	
L(mm) ±	4.5±0.3
W(mm) ±	4.0±0.3
T(mm) ±	3.2±0.3
Inductance(uH)	100
Tolerance(±%)	20
Test Frequency	1kHz,1 V
RDC(Ω)Max	2
Isat(A)	0.4
Operating Temperature	−40℃～105℃(Including self - temperature rise)

Part Numbering | Dimensions | Packing | Recommended Pattern | Electrical Characteristics

Downloaded from Arrow.com.



Products

Power Inductor

EMI-Common Mode Choke

EMI-Bead

RF-Signal Inductor

RF-Passives/Antennas

LAN Transformer

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Investor

Financial Information

Corporate governance

Stakeholder Contacts

Downloaded from Arrow.com.

Media Center

New Products

Events

Product Notices

Contact Us

Contact Info

Contact Form

Join Chilisin

Terms of Use

Privacy policy

Sitemap





Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.