



PRODUCT DETAILS

[Find More Products ▶](#)
[Request More Info](#)

Part Number

TM028HDHG59-01

Diagonal Size (in)	2.8
Pixel Resolution	240 x 320
Interface	RGB
Display Mode	TN
Technology	a-Si
Display Module Size (mm)	49.90 x 66.10 x 2.70
Display Active Area (mm)	43.20 x 57.60
Aspect Ratio	4:3
Backlight Luminance (nits)	300
LED Driver	No
Contrast Ratio	500:1
Viewing Angles (T/B/L/R)	70/60/70/70
Driver IC	ST7362
Response Time (ms)	20
Operating Temperature (°C)	-20 to +70
Touch Panel	No

Others

