





NO.	DESCRIPTION	PART NO.	QTY	MATERIAL	DRW NO.	REMARKS
1	INSULATOR		1	HEAT RESISTING RESIN		COLOR: WHITE UL94V-0
2	ACTUATOR		1	HEAT RESISTING RESIN		COLOR: BLACK UL94V-0
3	CONTACT		—	PHOS-BRONZE		t=0.12 AU PLATING
4	ANCHOR LOCK		2	SUS		t=0.15 AU PLATING



極数 NO. OF POS.	A	B	C	D	E
10	4.5	8.7	9.1	7.2	5.7
24	11.5	15.7	16.1	14.2	12.7
30	14.5	18.7	19.1	17.2	15.7
40	19.5	23.7	24.1	22.2	20.7
41	20.0	24.2	24.6	22.7	21.2
51	25.0	29.2	29.6	27.7	26.2
61	30.0	34.2	34.6	32.7	31.2


※この表は1, 2ページ目にのみ適用
※THIS CHART IS APPLICABLE TO
SHEET-1 AND SHEET-2 ONLY.

TOLERANCE / 一般公差(S)		PRODUCT SPEC / 製品規格							
X <10 ±0.2 10 ≤ X <30 ±0.25 30 ≤ X ±0.3		UNIT mm		ANGLE 3RD		A DCN-1127 10-20-14			
ANGLE / 角度 ±3°		SCALE N/S		DATE 8-09-11		O EDN-590 8-09-11	Y. MANBA	A. TSUNEMURA	T. SATOH
DRAWN Y. MANBA		DESIGNED Y. MANBA		CHECKED A. TSUNEMURA		APPROVED T. SATOH		NO. EDN/DCN DATE ISSUE CHECKED APPROVED	
						PART NAME / 品名 SERIES 6882 0.5mm PITCH FPC/FFC CONN. ASSY RA SMT			
						PART NO. / 型番 04 6882 XXX 099 846 +			
						DWG NO. / 図番 BJS 6882011		SHEET/REV 1/3 A	



ROHS規制対応
COMPLIANT WITH
ROHS REGULATIONS

KYOCERA KYOCERA Connector Products Corporation

NO.	DESCRIPTION	PART NO.	QTY	MATERIAL	DRW NO.	REMARKS
-----	-------------	----------	-----	----------	---------	---------






適合FPC/FFC寸法
APPLICABLE FPC/FFC



注 記
NOTE
① 適用FPC/FFC寸法は1か2を選択のこと。
SELECT AN APPLICABLE FPC/FFC FROM 1 OR 2.

ROHS規制対応
COMPLIANT WITH
ROHS REGULATIONS


TOLERANCE / 一般公差 (S)		PRODUCT SPEC / 製品規格											
X <10 ±0.2 10≤ X <30 ±0.25 30≤ X ±0.3 ANGLE / 角度 ±3°		UNIT		ANGLE		REFER		TO SHEET	1/3				
		mm		3RD		NO.		EDN/DCN	DATE	ISSUE	CHECKED	APPROVED	
		SCALE		DATE		PART NAME / 品名							
		NTS		8-09-11		SERIES 6882 0.5mm PITCH FPC/FFC CONN. ASSY RA SMT							
DRAWN	DESIGNED	CHECKED		APPROVED		PART NO. / 型番							
Y. MANBA	Y. MANBA	A. TSUNEMURA		T. SATOH		04 6882 XXX 099 846 +							
 KYOCERA Connector Products Corporation						DWG NO. / 図番					SHEET/REV		
						BJS 6882011					12/3 A		




NO.	DESCRIPTION	PART NO.	QTY	MATERIAL	DRW NO.	REMARKS
1	CONNECTOR	04 6882 XXX 099 846 +	1000	—		00 6882 XXX 099 846 +
2	EMBOSSSED TAPE		1	POLYSTYRENE		
3	TOP COVER TAPE		1	POLYSTYRENE		
4	REEL		1	POLYSTYRENE		

注 記
NOTE

- 梱包数量 : 1000 個/リール
PACKING QUANTITY : 1000 ea/reel
- 納入時のリール巻き方向
REELING DIRECTION
IN DELIVERY



- 引出し方向



- 型 番
P/N

04 6882 XXX 099 846 +

- バリエーション
VARIATION
- 1: テール防塵機能なし
WITHOUT TAIL DUST COVER
 - 3: テール防塵機能あり
WITH TAIL DUST COVER

極 数
NO. OF POS.

極 数 NO. OF POS.	A	B	C	D
10	11.5	—	24.0	30.4
24	14.2	28.4	32.0	38.4
30	14.2	28.4	32.0	38.4
40	20.2	40.4	44.0	50.4
41	20.2	40.4	44.0	50.4
51	20.2	40.4	44.0	50.4
61	26.2	52.4	56.0	62.4

※この表は3ページ目にも適用
※THIS CHART IS APPLICABLE TO
SHEET-3 ONLY.

※この注記の1～3は3ページ目にも適用

※THIS NOTES 1 TO 3 ARE APPLICABLE TO SHEET-3 ONLY.

ROHS規制対応
COMPLIANT WITH
ROHS REGULATIONS

TOLERANCE / 一般公差 (S)		PRODUCT SPEC / 製品規格			
X < 10 ±0.2		POLYSTYRENE (CLEAR)			
10 ≤ X < 30 ±0.25		UNIT	ANGLE	REFER TO SHEET 1/3	
30 ≤ X ±0.3		mm	3RD	NO.	EDN/DCN
ANGLE / 角度		SCALE	DATE	DATE	ISSUE
±3°		N/S	8-09-11	CHECKED	APPROVED
DRAWN	DESIGNED	CHECKED	APPROVED	PART NAME / 品名	
Y. MANBA	Y. MANBA	A. TSUNEMURA	T. SATOH	SERIES 6882 0.5mm PITCH FPC/FFC EMBOSS ASSY RA SMT	
		PART NO. / 型番		PART NO. / 型番	
		04 6882 XXX 099 846 +		04 6882 XXX 099 846 +	
		DWG NO. / 図番		SHEET / REV	
		BJS 6882011		13/3 A	

KYOCERA KYOCERA Connector Products Corporation