

ENCLOSURE HARDWARE

LED INDICATORS

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING

SOLUTIONS

RESOURCES

FLP25R5.0-SUR



Flexible Light Pipe Assembly, 2mm. Fiber Optic Core, Right Angle, 7mm. Dia. Low Profile Lens, 5.0in. Length, 3mm LED, Super Ultra Red



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES	VALUE ADDED	CHECK STOCK
- Wavelength: 640nm, Typical Intensity: 200mcd, Color: Red - Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED 7mm. Diameter Low Profile Lens Cap - Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info - Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear - Front Panel Mount Lens		

ecia
MEMBER

Enclosure Hardware

LED Indicators

LED Lighting

New Products

Locate a Distributor / Sales REP

Quality Assurance / RoHS

Product Info Center

Terms & Conditions

My Bivar

ESOP

100% Employee Owned