



Part Number : [1201000002](#)

Product Description : Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Male

Series Number : 120100

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : BA5S06-32


Documents and Resources

Drawings

[1201000002 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/01/2018 (15 January 2018)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120100
Description	Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Male
IP Rating	IP67
Product Name	Micro-Change (M12),PROFIBUS
Type	Field Attachable Connector
UPC	78678850052

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Reverse
Material - Connector Body	N/A
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver

Net Weight	48.534/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size (AWG)	22

This document was generated on Dec 25, 2025