



Part Number : [638279500](#)
Product Description : Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[638279500-000.pdf](#)
[TM-638000029-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	KK
Tool Type	Hand Crimp Tool
UPC	191128862158
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	576.034/g
------------	-----------

Applicable Parts

Description	Part Number
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass Tin (Sn)	<u>08500105</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass Tin (Sn)	<u>08500106</u>
KK Crimp Terminal, Series 2477, Humpback, with Tin (Sn) Plated Brass Contact, 24-18 AWG, Reel	<u>08500109</u>
KK Crimp Terminal, Series 2477, Humpback, with Tin (Sn) Plated Brass Contact, 24-18 AWG, Loose	<u>08500110</u>
3.96mm Pitch KK Crimp Terminal 2878, 20-18 AWG, Reel, Brass, Tin (Sn), Bifurcated	<u>08500115</u>
3.96mm Pitch KK Crimp Terminal 2878, 20-18 AWG, Bag, Brass, Tin (Sn), Bifurcated	<u>08500116</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 3.8µm Tin (Sn)	<u>08500119</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 3.8µm Tin (Sn)	<u>08500120</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Brass Tin (Sn)	<u>08500187</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Brass Tin (Sn)	<u>08500189</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 3.87µm Tin (Sn)	<u>08500281</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, Tin (Sn)	<u>08520071</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, Tin (Sn)	<u>08520072</u>

KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Phosphor Bronze Tin(Sn)	<u>08520112</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Phosphor Bronze Tin (Sn)	<u>08520113</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 5.0µm Tin (Sn)	<u>08520811</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 5.0µm Tin (Sn)	<u>08520812</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.38µm Selective Gold (Au)	<u>08550103</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.38µm Selective Gold (Au)	<u>08550104</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.76µm Gold (Au)	<u>08550133</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.76µm Gold (Au)	<u>08550134</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.51µm Selective Gold (Au)	<u>08560105</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.51µm Selective Gold (Au)	<u>08560106</u>
KK Crimp Terminal, Series 2477, Humpback, with Overall Gold (Au) Plated Brass Contact, 24-18 AWG, Reel	<u>08560113</u>
KK Crimp Terminal, Series 2477, Humpback, with Overall Gold (Au) Plated Brass Contact, 24-18 AWG, Loose	<u>08560114</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Selective Gold (Au)	<u>08580110</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Selective Gold (Au)	<u>08580111</u>

KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.76µm Gold (Au)	<u>08580114</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.76µm Gold (Au)	<u>08580115</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au)	<u>08580121</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.51µm Selective Gold (Au)	<u>08580122</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Gold (Au)	<u>08580187</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Gold(Au)	<u>08580189</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650114</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650115</u>
3.96mm Pitch KK Crimp Terminal 2878, 20-18 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au), Bifurcated	<u>08650118</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.9µm Pre-Plated Tin (Sn)	<u>39000286</u>
3.96mm Pitch EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 20-18 AWG, Reel	<u>1721601803</u>

This document was generated on Sep 23, 2025