Part Number : 192030389
Product Description : Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5)
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals



Documents and Resources

Drawings

192030389_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	822348424788

Agency

UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Net Weight	1.180/g
Packaging Type	Carton
Stud Size	10 (M5)
Temperature Range - Operating	483°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.70mm max.
Wire Size (AWG)	10, 12
Wire Size mm^2	4.00-6.00

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm^2 - 0.5mm^2	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.