




+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
2052 3356 00
Subminiature Coax | SM , SMA

1052633-1
TE Internal Number: 1052633-1
Alias ID: 2052-3356-00

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface SMA

Connector Style Jack

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Impedance (Ω) 50

Operating Frequency (GHz) 18

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

OSM 2 HOLE FLANGE MOUNT JACK RECEPTACLE WITH EMI/RFI GASKET
PDF (TIFF AVAILABLE)
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA
Connector Style Jack

Electrical Characteristics

Impedance (Ω) 50

Body Features

Cable Connector Orientation Straight
Body Material Stainless Steel
Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold over Copper
Center Contact Material Beryllium Copper
Connector Product Type Connector Assembly
RF Connector Contact Configuration Captivated Contacts

Mechanical Attachment

Panel Mount Retention Type Flange
Connector Mounting Type Panel
Panel Attachment Style Front Mount

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]
Pin Diameter Accepted .46 mm [.018 in]
Length 9.53 mm [.375 in]

Operation/Application

Operating Frequency (GHz) 18

Packaging Features

Packaging Method Bag

Other

Dielectric Material TFE Fluorocarbon
Number of Panel Mounting Holes 2
Gasket Material Conductive Elastomers
Comment Captured Center Contact

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF

