



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0156	2008/09/15	Shin	Add Notes
C	LEN1610005	2015/12/25	Kaven	Update Logo
D	C190268	2019/02/19	Ruru	Modify Note

ALTW
CONFIDENTIAL
2019-02-19
R&D DEPT.











Pin Assignments
Front View



Recommended Panel Cut-Out



Note: D
* QC Important Dimension.
* Waterproof Rate: IP67, Unmated
* Housing: Thermoplastic, Black
* Pin: Copper Alloy, Gold Plated
* Nut: Thermoplastic, Black
* Gasket: Rubber, Black
B * Use with waterproof cap or dust cap
Panel Thickness max: 2.5mm
B * Use without waterproof cap or dust cap
Panel Thickness max: 3.5mm
* Gasket and Nut are packed separately in PE bags.

UNIT: mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE: Mini Panel Lock 6Pin M Conn M Pin
SCALE: 2:1 | SIZE: A4 | SHEET: 1 OF 1
REV.: D | WC-REV.: A.6 | QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO: AU-06PMMS-LC7001	DRAWN BY: Ruru	DATE: 2019-02-19
DWG NO: AU-06PMMS-LC7001	CHECKED BY: Rita	DATE: 2019-02-19
CUSTOMER: ALTW	APPROVED BY: Max	DATE: 2019-02-19

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Downloaded from Arrow.com.