




REVISIONS 変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F5	REVISED PER ECR-23-175866	22MAY2023	DB	RE

-1; AS SHOWN



OBSOLETE

1 APPLICABLE SLEEVE P/N: 1717269, 178708

1 適用スリーブ型番: 1717269, 178708

PRE TIN HIGH HEAT RESISTANCE COPPER ALLOY 0.3t 錫めっき済み高耐熱銅合金 0.3t	175019-6
PRE TINNED PHOSPHOR BRONZE 0.3t 錫めっき済み燐青銅 0.3t	175019-5
PRE TINNED BRASS 0.3t 錫めっき済み黄銅 0.3t	175019-1
MATERIAL 材質	P/N 型番
WIRE RANGE 抱合電線断面積	AWG #22-#16 0.3~1.42 mm ²
INSULATION DIA 被覆外径	1.5~4.32 mm ϕ



TE Connectivity

NAME 名称				187 SERIES FLAG POSITIVE LOCK-EX REC. 187 シリーズ・旗型・ポジティブロック EX リセブタクル	
SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO		
A3	00779	C-175019	-		
SCALE 尺度			SHEET 1 OF 1	REV F5	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.SUZUKI	07JUL1999
DIMENSIONS: 単位: 耗 mm		CHK M.SHINDO	07JUL1999
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD M.SHINDO	07JUL1999
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格	108-5250
FINISH 仕上		APPLICATION SPEC 取付適用規格	114-5118
MATERIAL 材料		WEIGHT	0.000000
表参照 SEE TABLE		CUSTOMER DRAWING	

GENERAL TOLERANCE 一般公差
10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°