

TIME DELAY RELAYS



Active

TE CONNECTIVITY
7024WEV=96VDC 20-200 SEC

7024WEV
TE Internal Number: 9-1437490-5

Not EU RoHS or ELV Compliant
[Find Compliant Alternatives](#)

Type of Control **Knob**

Input Voltage(VDC) **96**

Contact Current Rating(A) **10A@240VAC**

Mode of Operation **Off-Delay**

Delay Time **20 – 200 seconds**
[See All Features](#)

North America

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION

SAVE TO LIST

CHECK FOR TOOLING

FIND SIMILAR PRODUCTS

DOCUMENTATIONFEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Relay Type	Time Delay
	Product Category	Electromechanical Relays
	Product Type	Relay
Configuration Features	Multiple Timing Ranges	Without
Electrical Characteristics	Input Voltage(VDC)	96
Contact Features	Type of Control	Knob
	Contact Current Rating(A)	10A@240VAC
	Delay Time	20 – 200 seconds
	Contact Arrangement	4 Form C, 4PDT, 4 C/O
Termination Features	Termination Type	Screw Terminal
Mechanical Attachment	Mounting Type	Mounting Bracket
Dimensions	Dimensions (L x W x H) (Approximate)	114.8 x 65.3 x 71.9mm[4.523 x 2.572 x 2.832in]
Usage Conditions	Operating Temperature Range(°C)	-30 – 75
Operation/Application	Mode of Operation	Off-Delay
Other	Repeatability (Max)	±5%
	Option	Transient/Surge Protection
Product Compliance	Statement of Compliance	
	PDF	
VIEW ALL PRODUCT COMPLIANCE		

COMPATIBLE

No compatible products found for 7024WEV