Your Expert Partner for **Human Machine Interfaces**

Indicator element

84-8001.5620



https://www.eao.com/component/84-8001.5620/en...

Downloaded from Arrow.com.

Your product:



84-8001.5620
Indicator element

OPERATING-/INDICATION PART

Illumination colour: Green

ELECTRICAL CHARACTERISTICS

Forward voltage:

Operating voltage: 24 V DC ±10 %

MECHANICAL CHARACTERISTICS

Terminal: Plug-in terminal, 2.8 x 0.8 mm

Weight: 0.006 kg

AMBIENT CONDITION

IP Protection: IP40

CERTIFICATE

Approbations: UL

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Indicator element, Green, Single-LED, 24 V DC ±10 %, Plug-in terminal, 2.8 x 0.8 mm


Kind of illlumination: Single-LED

Hints: LED and built-in resistor included

Downloaded from Arrow.com.

Standard version: Cable length 300 mm
Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67)
Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occure, the plugs may become loose
Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED
For use on a flat surface of a Type 4X enclosure – FOR INDOOR USE ONLY

Wiring diagrams:



Downloaded from Arrow.com.