





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/10	
A		UPDATE SPEC.	6/27/16	AY/SC



SPECIFICATIONS:

Material:

Insulator: NY66, rated UL 94V-0

Insulator color: Natural

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 3A AC/DC max, 22AWG

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15

A = .079 [2.00] x No. of Spaces

B = .079 [2.00] x No. of Spaces + .157 [4.00]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	11/23/10
CHECKED	AH	11/23/10
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE			
.079 [2.00] CRIMP HOUSING			
SIZE X	PART NO. 2CH-H-XX	REV. A	
REF: S00015T	SCALE: NTS	SHEET 1 OF 1	