



**TJ xx 71x 0 xxxx G**

No. OF POLES  
 02 2 CONTACTS  
 03 3 CONTACTS  
 ... ..  
 24 24 CONTACTS

COLOR  
 0 Black (RAL9005)  
 2 Red (RAL3001/D)  
 3 Orange(RAL2011/P)  
 4 Yellow(RAL1018/A)  
 5 Green(RAL6018/T)  
 6 Blue (RAL5015/A)  
 8 Grey(RAL 7035/D)  
 9 White(RAL1102)  
 C Green(RAL6018/U)

G RoHS compliant (lead<4%)  
 In copper Alloy  
 00Y0: "@" Logo (Standard)  
 00YA: "ANYTEK" Mark  
 Any special item by customer request. please contact sales department.



Dimension		N= Number of poles	
		Poles	Tolerance
Dim L	N×5.0	2P-7P	±0.15
Dim B	(N-1)×5.0	8P-12P	±0.25
Dim C	N×5.0±0.10	13P-18P	±0.30
		19P-24P	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	02/03'05	Part No. changed.	Marvin
△	06/26'06	Solid/Stranded wire(AWG) is changed from 12-22 to 12-24	Marvin
△	8/10'06	Added VDE and TUV standard	梁仁松
△	12/17'08	Add the tolerance table	Jacke
△	12/17'08	The temperature changed from -30°C,+105°C to -40°C,+115°C	Jacke
△	03/08'10	Add the 2P mark	Jacke
△	04/03'14	Update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

### Material

- Item① Clamp: Brass(CuZn) Ni plated
- Item② Terminal screw: Steel Zinc plating "-" slot type
- Item③ Female contact: PhBz ,Tin plated
- Item④ Terminal Cover: Thermoplastic (UL94V-0)
- Item⑤ Terminal housing: Thermoplastic (UL94V-0)


### Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 20A/20A/20A
- Wire range: 2.5mm<sup>2</sup>/0.34-2.5mm<sup>2</sup>
- Solid wire(AWG): 12-24/14-22
- Stranded wire(AWG): 12-24/14-22
- Torque: 5Lb-In/0.5Nm/0.56Nm
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus VDE TUV
- Critical dimension: △

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ-5.00mm Series						
PART NO.		TJxx71x0xxxxG			DWG NO.	8TJ0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Chen Bo 04/03 '14	Chen Bo 04/03 '14		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
				SHEET: 01/01	REV: H		X.XX	±0.10
							X°	±1°

UNIT: mm  
 SCALE: NONE  
 SHEET: 01/01  
 REV.: H