<img height="1" width="1" style="display:none;" alt="" src="https://dc.ads.linkedin.com/collect/?pid=39563&fmt=gif"> <img height="1" width="1" style="display:none" src="https://www.facebook.com/tr?id=890724887782932&ev=PageView&noscript=1">

UTP28X7GR

Share

Copper Patch Cord

Category 6A Performance, 28AWG, UTP Patch Cord, CM/LSZH, Green, 7ft.

Find A Distributor

Qty

Add to Bom

Specifications | Packaging Detail | Resources

Related Products | Top of Page

Specifications

Conductor Gauge (AWG)	28

Downloaded from Arrow.com.

Performance Level	Category 6A
Conductor Type	Solid
Overall Length (In.)	NA
Overall Length (ft.)	7
Overall Length (m)	2.1
Overall Length (mm)	NA
Nominal Diameter (mm)	NA
Wiring Scheme	T568B
Maximum Operating Temperature (°C)	75
Maximum Operating Temperature (°F)	167
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Boot Color	Clear
Color	Green
Sub Brand	PanNet
Flammability Rating	CM, LSZH-1 (60332-1)
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Product Type	Copper Patch Cord
Cable Color	Green
Length (ft.)	7.00
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.19
Nominal Cable Outside	4.7

Downloaded from Arrow.com.

Diameter (mm)	
Cable Length (ft.)	7.00
Cable Type	F/UTP
Conductor Material	Copper
Material	Copper
Maximum Installation Temperature (°C)	70
Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	-40
Minimum Installation Temperature (°F)	-40
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
Measurement System	Feet (USA Only)

Packaging Detail

UPC	07498304901
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0170
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	0.1703


Resources

Technical References	Patch Cord Wiring Guide: TR103	US English	View PDF (262.81KB)	Download PDF	Share PDF
Selection Guides	Patch Cord Selection Guide (All Regions): COSG11--WW-ENG	US English	View PDF (292.58KB)	Download PDF	Share PDF

Downloaded from Arrow.com.


Specification Sheets	TX6A-28™ Category 6A Performance 28 AWG UTP Patch Cords	US English	View PDF (190.34KB)	Download PDF	Share PDF
Part Drawings	Category 6A UTP 28 AWG Copper Patch Cords - (CM/LSZH)	US English	View PDF (301.53KB)	Download PDF	Share PDF
Selection Guides	28 AWG Selection Guide - Category 6A, 6, & 5e (NA, LA): COSG10--WW-ENG	US English	View PDF (631.55KB)	Download PDF	Share PDF
Installation Documents	Panduit 28 AWG Patch Cords Installation Guideline	US English	View PDF (198.34KB)	Download PDF	Share PDF

Related Products



UTPSP7BUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 7 ft.



UTPSP2MBUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 2 meters.

Downloaded from Arrow.com.

UTPSP5BUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 5 ft.

Email Support

Email support available 24/7

800-777-3300

Monday through Thursday 7:00 am-6:30 pm CST Friday 7:00 am-6:00 pm CST

Where to Buy

Find a Panduit Distributor or Partner

Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like

Download

Copyright 2019 Panduit

Legal Information Privacy Policy Unsubscribe

Downloaded from Arrow.com.