

Shrinkable markers, "Continuous Tube", thermal transfer

TCGT – 3:1 Commercial Grade

TCGT is a commercial grade 3:1 heat shrink marker material supplied as a continuous tube and printable on both sides. TCGT's polyolefin compound has good mechanical strength and resistance to organic solvents and chemicals. The surface of the tubing has been especially prepared so that print performance is excellent at all times. HellermannTyton's printer range allow users to create a high quality print. In addition it is possible to either perforate the tubing at pre-determined lengths or fully sever the markers.

Features and benefits

- Shrink ratio 3:1
- Available in black, blue, red, white and yellow
- Cable range from 39 mm to 1 mm
- Good mechanical strength and resistance to organic solvents and chemicals
- Highly flexible
- Delivery in convenient storage boxes



TCGT – five colours of printable tube to cover a wide range of diameters.



TCGT continuous tube – printable on both sides.



For size matrix please refer to page 452.

MATERIAL	Polyolefin, cross-linked (PO-X)
Operating Temperature	-55 °C to +135 °C
Min. Shrink Temperature	+90 °C
Shrink Ratio	3:1
Recommended Ribbon Type	TTDTHOUT, TTRW, TT822OUT8
Thermal Transfer Printer	TT431, TT4030, TrakMark DS



RoHS ✓

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TCGT3-1BK	3.0	1.0	0.56	176 m	Black (BK)	553-30352
TCGT3-1BU	3.0	1.0	0.56	176 m	Blue (BU)	553-30353
TCGT3-1RD	3.0	1.0	0.56	176 m	Red (RD)	553-30354
TCGT3-1WH	3.0	1.0	0.56	176 m	White (WH)	553-30351
TCGT3-1YE	3.0	1.0	0.56	176 m	Yellow (YE)	553-30350

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.
More colours on request.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!
www.HT.click/9-461

HellermannTyton



Shrinkable markers, "Continuous Tube", thermal transfer

TCGT – 3:1 Commercial Grade



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TCGT4.8-1.6BK	4.8	1.6	0.56	110 m	Black (BK)	553-30452
TCGT4.8-1.6BU	4.8	1.6	0.56	110 m	Blue (BU)	553-30453
TCGT4.8-1.6RD	4.8	1.6	0.56	110 m	Red (RD)	553-30454
TCGT4.8-1.6WH	4.8	1.6	0.56	110 m	White (WH)	553-30451
TCGT4.8-1.6YE	4.8	1.6	0.56	110 m	Yellow (YE)	553-30450
TCGT6-2BK	6.0	2.0	0.64	110 m	Black (BK)	553-30652
TCGT6-2BU	6.0	2.0	0.64	110 m	Blue (BU)	553-30653
TCGT6-2RD	6.0	2.0	0.64	110 m	Red (RD)	553-30654
TCGT6-2WH	6.0	2.0	0.64	110 m	White (WH)	553-30651
TCGT6-2YE	6.0	2.0	0.64	110 m	Yellow (YE)	553-30650
TCGT9-3BK	9.0	3.0	0.64	72 m	Black (BK)	553-30952
TCGT9-3BU	9.0	3.0	0.64	72 m	Blue (BU)	553-30953
TCGT9-3RD	9.0	3.0	0.64	72 m	Red (RD)	553-30954
TCGT9-3WH	9.0	3.0	0.64	72 m	White (WH)	553-30951
TCGT9-3YE	9.0	3.0	0.64	72 m	Yellow (YE)	553-30950
TCGT12-4BK	12.0	4.0	0.68	54 m	Black (BK)	553-31252
TCGT12-4BU	12.0	4.0	0.68	54 m	Blue (BU)	553-31253
TCGT12-4RD	12.0	4.0	0.68	54 m	Red (RD)	553-31254
TCGT12-4WH	12.0	4.0	0.68	54 m	White (WH)	553-31251
TCGT12-4YE	12.0	4.0	0.68	54 m	Yellow (YE)	553-31250
TCGT18-6BK	18.0	6.0	0.90	26 m	Black (BK)	553-31852
TCGT18-6BU	18.0	6.0	0.90	26 m	Blue (BU)	553-31853
TCGT18-6RD	18.0	6.0	0.90	26 m	Red (RD)	553-31854
TCGT18-6WH	18.0	6.0	0.90	26 m	White (WH)	553-31851
TCGT18-6YE	18.0	6.0	0.90	26 m	Yellow (YE)	553-31850
TCGT24-8BK	24.0	8.0	0.98	26 m	Black (BK)	553-32452
TCGT24-8BU	24.0	8.0	0.98	26 m	Blue (BU)	553-32453
TCGT24-8RD	24.0	8.0	0.98	26 m	Red (RD)	553-32454
TCGT24-8WH	24.0	8.0	0.98	26 m	White (WH)	553-32451
TCGT24-8YE	24.0	8.0	0.98	26 m	Yellow (YE)	553-32450
TCGT39-13BK	39.0	13.0	1.08	10 m	Black (BK)	553-33952
TCGT39-13BU	39.0	13.0	1.08	10 m	Blue (BU)	553-33953
TCGT39-13RD	39.0	13.0	1.08	10 m	Red (RD)	553-33954
TCGT39-13WH	39.0	13.0	1.08	10 m	White (WH)	553-33951
TCGT39-13YE	39.0	13.0	1.08	10 m	Yellow (YE)	553-33950

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.
More colours on request.



For product specific approvals and specifications please refer to the Appendix.

