

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	C	MOLD DUPLICATION	25AUG2005	LCi	JDr

COUPE A - A

CE PLAN EST UN EXTRAIT DU
PLAN DE DEFINITION, ON FERA
REFERENCE AU PLAN DE
DEFINITION POUR TOUT LITIGE

NUMERO DE VOIE
WAY NUMBER



SPECIFICATIONS FI PC/PL

CLIP UZ15	CLIP CuNiSi
1544141	1544128
FI < 60N	FI < 70N

REF LANGUETTE 8MM

TE	PSA	RENAULT
1544509-1	92 550 251 80	-
1544452-1	92 550 116 80	7701 997 036
1544453-1	92 550 126 80	7701 997 037

PRC	TE REF	PSA REF	RENAULT REF	COULEUR	CODAGE
B	1544459-1	96 111 357 80	7703 297 722	NOIR	
B	1544459-2	96 111 358 60	7703 297 721	GRIS	
B	1544459-3	96 111 358 80	-	MARRON	



NOTES :

FI LANGUETTE SANS VS < 30 N
FE LANGUETTE SANS VS > 80 N
FE LANGUETTE AVEC VS > 100 N

DATEUR
DATE CODE (YEAR/MONTH)

INDICE PIECE
PART REVISION

MATIERE
MATERIAL

EMPREINTE
CAVITY NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. CE PLAN EST UN DOCUMENT CONTROLE PAR AMP INCORPORATED. IL EST SUSCEPTIBLE D'ETRE REVISE. CONTACTER LE SERVICE TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIERE REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 1. PLC/DEC: ± 2. PLC/DEC: ± 3. PLC/DEC: ± PLC/DEC: ± ANGLES ±3°
MATERIAL MATIERE PA 66	FINISH FINITION -

DWN /DESSINE L. CORONELLI CHK /VERIFIE P. FLORES APVD /APPROUVE J. DAHER	25AUG2005 25AUG2005 25AUG2005
PRODUCT SPEC SPEC. PRODUIT APPLICATION SPEC SPEC. APPLICATION	- -
WEIGHT MASSE APPROX.	6 g
CUSTOMER DRAWING /PLAN CLIENT	

Tyco Electronics France SAS RN 90, 38530 Chapareillian		NAME TYPE	
PORTE LANGUETTE 2 VOIES 8 mm A VS 2 WAYS TAB HOUSING WITH SECONDARY LOCK		RESTRICTED TO RESERVE A	
SIZE FORMAT A3	CAGE CODE 00779	DRAWING NO No PLAN C=1544459	
UNIQUEMENT POUR REFERENCE		SCALE ECHELLE 2:1	SHEET FEUILLE 1 OF DE 1 REV C