**Part Number :** 936010197
**Product Description :** Heavy-Duty Screw Terminal Insert, Female, 4-Pole, 80A, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»
**Series Number :** 93601
**Status :** Active
**Product Category :** Heavy-Duty Connectors
**Engineering Part Number :** 7304.6044.0



## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Heavy Duty Connectors |
| Series | 93601 |
| Description | Heavy-Duty Screw Terminal Insert, Female, 4-Pole, 80A, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27» |
| Component Type | Inserts - Screw Terminal |
| Insert Series | S-K4/0 |
| Product Name | Heavy-Duty Connectors |
| Standard | CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977 |
| UPC | 887191876054 |

### Agency

| | |
|---|---|
| UL | E249674 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 80.0A |
| Voltage - Maximum | 830V |
| Wire Protection | Yes |

### Physical

| | |
|---|---|
| Component Size | 16B «77X27» |
| Durability (mating cycles max) | 500 |
| Gender | Female |
| Insert Color | Grey |
| Material - Contact | Copper Alloy |
| Material - Insert | Polycarbonate |
| Material - Plating | Silver |

Downloaded from Arrow.com.

| | |
|---|---|
| Net Weight | 116.300/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Polarized to Mating Part | Yes |
| Poles | 4 |
| Stripping Length | 14.00mm, 7.00mm |
| Temperature Range - Operating | -40° to +125°C |
| Tightening Test Torque | 0.50 Nm, 2.50 Nm |
| Wire Size (AWG) | 14-20, 5-16 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Heavy-Duty Screw Terminal Insert, Male, 4-Pole, 80A, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27» | 936010198 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Use With | Size 16B «77x27» Hoods and Housings |



Downloaded from Arrow.com.