





REV.	DATE	DESCRIPTION
A	07/31/98	MODIFY CONTACT PIN I.D.
B	05/09/07	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .213"
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .100"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	05/09/07										
6						CHECKED												
5						ISSUED				PART DESCRIPTION								
4	FERRULE	BRASS	NICKEL	1						N CRIMP REVERSE POLARITY PLUG (RG-58/U CABLE)								
3	CONTACT PIN	PHOS. BRONZE	GOLD	1						PART NO.								
2	INSULATOR	TEFLON	NATURAL	1						172100RP								
1	HOUSING/BODY	BRASS	NICKEL	1						DWG. NO.		172100RP.DWG	REV.	B	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE			C:/172/172100RP.DWG								