

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMW
XYR6000™

[find out more](#)

white papers

Wireless Switches Offer
Unlimited Benefit
Basic Switches Are Not Created
Equal
Applying Precision Switches
Sensors for Medical Devices
New Ways to Measure Torque
Choosing Safety Switches
Specifying Hour Meters

Need help?

[Click here to contact us](#)

BZ-R291-P4

(Home : Products : Switches » MICRO SWITCH™ Basic Switches »
Premium Large Basic Switches » BZ/BA/WA/YZ)



Actual product appearance
may vary.
[click here to download Hi-Res image](#)

BZ Series Standard Basic Switch, Single Pole Double Throw
Circuitry, 15 A at 250 Vac, Pin Plunger Actuator, Screw
Termination, Silver Contacts, UL, CSA, ENEC

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Pin Plunger
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Force (OF)	2,5 N [9.0 oz] max.
Release Force	1,11 N [4.0 oz] min.
Overtravel (OT)	0,13 mm [0.005 in] min.
Differential Travel (DT)	0,005 mm [0.0002 in] max.
Material	Plastic
Housing Material	General Purpose Phenolic
High Temperature	85 °C [185 °F]
Agency Approvals and Standards	UL, CSA, ENEC
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	24,94 g to 34,01 g [0.055 lb to 0.075 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370; Left-side facing #8 screw with cupwasher integral construction
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BA/WA/YZ

contacts

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

Meet Dr. Larry



my links

Login to iCOM
Login to Rep/AD Portal
Login to Digital University

News Center

HONEYWELL ANNOUNCES
ADDITION TO RELIALIGN™
RESIDENTIAL DOOR
INTERLOCK SWITCHES THAT
FEATURE RUGGED, PLASTIC
HOUSING

HONEYWELL RELEASES
UNLIMITED POTENTIAL WITH
NEW LIMITLESS™ WIRELESS
SWITCHES

HONEYWELL'S XYR6000
WIRELESS POSITION SENSOR
ENABLES MONITORING IN
HAZARDOUS AREAS AND
REMOTE LOCATIONS

**MICRO SWITCH
Anniversary site**