




| Item              | Code                     | Spec        |         |
|-------------------|--------------------------|-------------|---------|
| NO of PIN         | N                        | 4           |         |
| Pitch             | P                        | 0.5±0.05    |         |
| Total Length      | L                        | 51±1        |         |
| Margin            | M                        | 0.5±0.05    |         |
| <b>Thickness</b>  | T                        | 0.3±0.03    |         |
| Strip Length      | S1                       | 3.5±0.5     |         |
|                   | S2                       | 3.5±0.5     |         |
| Supporting Length | D1                       | 6.0±1.0     |         |
|                   | D2                       | 6.0±1.0     |         |
| Total Pitch       | TP                       | 1.5±0.05    |         |
| Total Width       | W                        | 2.5±0.05    |         |
| Conductors        | Width                    | 0.3±0.03    |         |
|                   | Thickness                | 0.035±0.005 |         |
|                   | Plated                   | Sn(1um)     | Min     |
| Film              | White                    |             | 0.06mm  |
|                   | White                    |             | 0.06mm  |
| Supporting        | Blue                     |             | 0.225mm |
| UL NO.            | <b>UL20890(105℃ 90V)</b> |             |         |

Processing requirement:

CnC Tech, LLC

## Industrial Cable and Connector Technology

|              |                     |                                               |          |                                                                                       |
|--------------|---------------------|-----------------------------------------------|----------|---------------------------------------------------------------------------------------|
| DRAWN BY:    | DATE:<br>2018/07/20 | DESCRIPTION:<br>4-51-0. 5-3. 5/3. 5-6/6-A-Tin |          |                                                                                       |
| CHECKED BY:  | SHEET 1 of 1        | ITEM NO. 310-04-0051                          |          |                                                                                       |
| APPROVED BY: | SCALE 1:1           | REV. A/0                                      | UNIT: mm |  |

|     |                           |        |         |
|-----|---------------------------|--------|---------|
|     |                           |        |         |
| 1.  |                           |        |         |
| NO. | Specification description | Number | Remarks |

