


REV.	DATE	DESCRIPTION
A	09/25/03	MODIFY BODY LAYOUT

DESCRIPTION
MODIFY BODY LAYOUT



Amphenol Connex									
PART DESCRIPTION									
N 50ohm MALE TO F 75ohm MALE ADAPTER									
PART NO. 242157									
DWG. NO. 242157.DWG									
REV. A SIZE A SCALE NA									
APPROVALS		DATE							
DRAWN G.R.S.		09/25/03							
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE IN THOUSITHS OF AN INCHES AND FOR CUSTOMER REFERENCE ONLY.									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:									
0.5 - 8mm ± 0.20mm									
8 - 30mm ± 0.40mm									
30 - 120mm ± 0.50mm									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:									
.020 - .315 = ± 0.007"									
.315 - 1.180 = ± 0.015"									
1.180 - 4.724 = ± 0.020"									
DO NOT SCALE DRAWING				CADD FILE C:/242/242157.DWG					
DESCRIPTION		MATERIAL		FINISH		QTY			
1 BODY		BRASS		NICKEL		1			
2 INSULATOR		TEFLON		NATURAL		1			
3 CONTACT PIN		BRASS		GOLD		1			
4									
5									
6									
7									
8									