

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Thermal transfer printer, Weight: 10 kg, Width: 242 mm, Height: 274 mm, Color: gray

Why buy this product

- ✓ High print speed
- ✓ This printer is suitable for labeling large quantities and processes all roll materials
- ✓ The easy-to-use centering function for the printing material makes it possible to label continuous media such as shrink sleeves
- ✓ High-quality resin-based ink ribbons ensure marking that is resistant to mechanical and chemical influences
- ✓ Print resolution of 300 dpi
- ✓ Continuous media can be cut and perforated with a high degree of positioning accuracy

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 484817
GTIN	4046356484817
Weight per Piece (excluding packing)	11.000 g
Custom tariff number	84433210
Country of origin	Germany

Technical data

General

Interface	Serial (RS-232)
	USB 2.0
Weight	10.00 kg

Dimensions

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Technical data

Dimensions

Length	446.00 mm
Height	274.00 mm
Width	242.00 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	24190103
eCl@ss 4.1	24190103
eCl@ss 5.0	19020205
eCl@ss 5.1	19020205
eCl@ss 6.0	19140107
eCl@ss 7.0	19140107
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 5.0	EC001672
ETIM 6.0	EC001672

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212108

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Approvals



Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00240
EAC		RU *- DE.A*30.B.02513

Accessories

Accessories

Documentation

Manual - UM IA THERMOMARK X1.2 - 2910774

Manual

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., Length: 300 m, Width: 110 mm, Color: black

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, Width: 110 mm, Color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, Width: 110 mm, Color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, Width: 110 mm, Color: red

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., Width: 110 mm, Color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., Width: 110 mm, Color: black

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), Width: 110 mm, Color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., Width: 64 mm, Color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), Width: 64 mm, Color: white

Ink ribbon - TM-RIBBON 110-TC/TR WH - 1014402



Ink ribbon, for roll printer and THERMOMARK CARD for printing product groups US-EMLF..., US-PML..., EMLF..., PML..., and EMLP..., Width: 110 mm, Color: white

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Accessories

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Printing system

Thermal transfer printer set - THERMOMARK X1.2-KIT - 5146341

Thermal transfer printer set

Printing system accessories

Cutter - THERMOMARK X1-CUTTER - 5145290



Cutter, for the THERMOMARK X1

Case - THERMOMARK X1-CASE - 5145300



Transport case for THERMOMARK X1 thermal transfer printer, rounded profile case with aluminum frame

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Thermal transfer printer - THERMOMARK X1.2 - 5146231

Accessories

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Cutter - THERMOMARK X1-CUTTER/P - 5146244



Cutter/perforation device, for the THERMOMARK X1

Accessories - THERMOMARK-CP - 5145371



Cleaning pen, for thermal transfer printers

Replacement part - THERMOMARK X1-ROLLER - 5146396

Replacement print roller for X1...printer