This document was generated on 09/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190840003
Status: Active
Overview: Solderless Terminals
Description: Open Barrel Star Ring, Brass, for 14-18 AWG Wire, Stud Size 10 (M5)



Series image - Reference only

Documents:
Drawing (PDF)
Product Specification PS-19902-006-001 (PDF)
Product Specification PS-19902-011-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19084
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Solderless Terminals
Product Name	N/A
Type	Ring
UPC	800753084803

Physical

Barrel Type	Open
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.691/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	14, 16, 18
Wire Size mm²	0.80-2.00

Material Info

Engineering Number	SRZ-0129-10

Reference - Drawing Numbers

Product Specification	PS-19902-006-001, PS-19902-011-001
Sales Drawing	SD-19084-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
19084 Series

This document was generated on 09/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.