

Product data sheet

Specifications



MGE Galaxy 3500 Input Transformer 208/208 10-30kVA Floormount

G35TXFM10K30F

⚠ Discontinued - Service only

⚠ Discontinued on: Nov 22, 2021

⚠ To be end-of-service on: Dec 31, 2031

Overview

Lead time Usually Ships within 2 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Rated power in VA	30000 VA
Provided equipment	Installation guide

Physical

Height	148.7 cm
Width	35.1 cm
Depth	83.7 cm
Net weight	280 kg
Mounting support	Floor
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency 60 Hz

Conformance

Standards	CSA C22.2 No 107.1 UL 1778
Product certifications	CSA

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	0...45 °C
Storage Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage altitude	0...9144 m
------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	314 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
EU RoHS Directive	Under investigation