
Part Number : 5013300631
Product Description : 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Single Row, Inner Positive Lock, 6 Circuits, Black
Series Number : 501330
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

5013300631_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

5013300631.dxf

Specifications

5013300000-AS-000.pdf

5013300000-AS-001.pdf

SPK-501330-001-001.pdf

5013300000-PS-001.pdf

5013300000-PS-003.pdf

5013300000-PS-004.pdf

5013301000-PS-001.pdf

5013301000-PS-003.pdf

5013301000-PS-004.pdf

PS-501331-001-001.pdf

PS-501568-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant

Downloaded from Arrow.com.

China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	501330
Description	1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Single Row, Inner Positive Lock, 6 Circuits, Black
Application	Signal, Wire-to-Board
Product Name	Pico-Clasp
UPC	884982298552

Agency

UL	E29179

Downloaded from Arrow.com.

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	63.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Pico-Clasp Vertical, Single Row, Surface Mount Headers	203556
Pico-Clasp Vertical, Single Row, Surface Mount Headers	203557
Pico-Clasp Vertical Single Row Headers	501331
Pico-Clasp Vertical Single Row Headers	504449
Pico-Clasp Right-Angle, Single Row, Surface Mount Headers	202396
Pico-Clasp Right-Angle, Single Row, Surface Mount Headers	203558
Pico-Clasp Right-Angle, Single Row, Surface Mount Headers	203559

Downloaded from Arrow.com.

Pico-Clasp Right-Angle Single Row Headers	501568
Pico-Clasp Vertical, Single Row, Surface Mount, Low-Halogen Headers	208381
Pico-Clasp Right-Angle, Single Row, Surface Mount, Low-Halogen Headers	208387

Use with Part(s)

Description	Part Number
Pico-Clasp Female Crimp Terminals	501193
Pico-Clasp Female Crimp Terminals	501334

Downloaded from Arrow.com.