Part Number : 936013797
Product Description : Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Double Top Entry, Size 24B «104x27», M32x2 Threads, Grey, High Construction
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7824.6625.5



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Double Top Entry, Size 24B «104x27», M32x2 Threads, Grey, High Construction
Component Type	Double Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191862149

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V

Physical

Component Size	24B «104X27»
Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	287.000/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M32x2
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

Downloaded from Arrow.com.