



HIRSCHMANN

A BELDEN BRAND

Product information BAT-ANT-N-9A-DS-IP65

Industrial Ethernet:Industrial Wireless LAN:Wireless Accessories :Wireless LAN Antennas:BAT-ANT-N-9A-DS-IP65

<https://catalog.beldensolutions.com:443/link/57078-24455-49859-24498-24499-65280/en/conf/ui/state>

Name	BAT-ANT-N-9A-DS-IP65
	
	directional diversity antenna linear for 5 GHz
Delivery informations	
Availability	available
Product description	
Description	directional diversity antenna linear for 5 GHz
Type	BAT-ANT-N-9A-DS-IP65
Order No.	943 981-010
Cable length	1 m
Cable specification	N plug to N plug
Radio technology	
Range	n/a
Frequency band	5150 MHz - 5875 MHz
Polarisation	dual linear, +/- 45° slant
Elevation, Azimuth	3 dB beam width 60° / 60°
VSWR	1.6
Gain	9 dBi
Antenna connector	N female
Ambient conditions	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	15 N at 160 km/h
Mechanical construction	
Dimensions (W x H x D)	101 mm x 80 mm x 35 mm
Mounting	wall, mast
Protection class	IP65
Material	LEXAN EXL 9330
Weight	0.11 kg
Scope of delivery and accessories	
Scope of delivery	antenna, 2x 1 m cable, mounting material, 2x Pigtail N to RP-SMA

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.