







Content D-Sub hood			Spare parts (MOQ100)	
Pos.	Quantity	Description	Part Number	Quantity
01	1	Housing:		
		either thermoplastic metallized housing (for 0967 050 0453)		
		or thermoplastic black housing (for 0967 050 0452)		
02	1	Cover:		
		either thermoplastic metallized cover (for 0967 050 0453)		
		or thermoplastic black cover (for 0967 050 0452)		
03	2	Blank piece:		
		either thermoplastic metallized blank piece (for 0967 050 0453)	0967 003 6013	1
		or thermoplastic black blank piece (for 0967 050 0452)		
04	4	Screws for cover		
05	2	Screws for cable clamp x6,5mm	0967 000 9944	1
		Screws for cable clamp x8,5mm (optional)	0967 000 9946	1
06	1	Cable clamp	0967 000 9943	1
07	2	Locking bolt	0967 003 6014	1

Cable diameter between 4 and 9mm, 11mm max. with longer cable clamp screws(0967 000 9946)
Cable clamp screws max. torque=0,3Nm
Cover screws max. torque=0,15Nm for 0967 050 0453
Cover screws max. torque=0,25Nm for 0967 050 0452

Part number	Description
0967 050 0453	D-Sub 50-pole thermoplastic metallized top and side entry hood for spring or slide locking
0967 050 0452	D-Sub 50-pole thermoplastic black top and side entry hood for spring or slide locking

All Dimensions in mm
Original Size DIN A3

Scale 2:1

Free size tol.

Ref.

Sub.

All rights reserved

Department EL PD

HARTING Electronics GmbH
D-32339 Espelkamp

Created by ZENGD

Inspected by LUOK

Standardisation HOFFMANN

Date 2019-11-06

State Final Release

Title D-Sub 50-pole plastic top and side entry hood

Doc-Key / ECM-Nr. 100673869/UGD/002/B 500000160261

Type TB

Number 0967050045Y

Rev. B

Page 1/1

Downloaded from Arrow.com.

A3