











DASH NO.	SOCKET BODY LENGTH INCH/MM	DIA "A" INCH/MM	DIA "B" INCH/MM	INPUT	OUTPUT	KIT #
-01	.100/2.54	.280/7.11	.280/7.11	18380	18392	18372
-02	.135/3.43	.315/8.00	.315/8.00	18381	18393	18373
-03	.160/4.06	.340/8.64	.340/8.64	21540	21545	21512

NOTE:
1. MATERIALS: INMATES: PPS RYTON 7
SOCKETS: BE-CU #25, Au PLATED.
2. FULLY SEAT SOCKET INTO INMATE HEADER.
3. ROHS COMPLIANT PER CST-0001 LATEST REVISION.



DRAWN BY
LAP NGUYEN

DATE
6/99

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE: INCH / (MM)

TOLERANCES ARE:
DECIMALS ANGLES
XXX (X.X) = ±0.01 (0.25) ±1°
X.XXX (X.XX) = ±0.005 (0.127)

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

SWD

DWG, VI700 INMATE, LN

SIZE
D 67131

CAGE CODE
20029-XX

DWG NO
20029-XX

REV
5

SCALE 4:1

SHEET 1 OF 1