





Rev	AWO #	Description	Date	Appr
-	-	RELEASED	12/15/06	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15
A = .079 [2.00] x No. of Positions + .153 [3.90]
B = .079 [2.00] x No. of Spaces
C = .079 [2.00] x No. of Positions + .024 [0.60]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

RIGHT ANGLE, SURROUNDED HEADER

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]				TITLE .079 [2.00] SHROUDED HEADER RIGHT ANGLE, SURFACE MOUNT			
TOLERANCES: EXCEPT AS NOTED	INCHES	HOLES	DATE	SIZE	PART NO.	REV.	REV.
.X ± .10	ØXX	± .10		X	2SH-C-XX-TR-SMT		
.XX ± .020	ØXXX	± .015					
.XXX ± .015	ØXXX	± .010					
APPROVALS							
DRAWN	BW	12/15/06					
CHECKED							
APPROVED							