

- 
- Products
- Industry Solutions
- CAREERS
- Resources
- Find Distributor
- Contact Molex



Part Number: 46437-1652

TEN60 R/A PLUG ASSY G-35S-G

Image not available

Series image - Reference only

Status: Active

Series: [46437](#)

Category: Molex Parts

Product Environmental Compliance

[EU ELV](#):Not Relevant

[EU RoHS](#):Compliant

[EU RoHS Phthalates](#):Not Contained

[China RoHS](#): 

[REACH SVHC](#):Not Contained Per -ED/01/2017 (12 January 2017)

[Low-Halogen Status](#):Low-Halogen

Part Detail

General

Status Active

Category Molex Parts

Series [46437](#)

UPC 887191608822

Physical

Flammability 94V-0

Net Weight 8.113/g

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA

LR19980

UL

E29179

Solder Process Data

[Solderability Shelf Life Statement](#)

Duration at Max. Process Temperature (seconds) 040

Lead-free Process Capability

SMC&WAVE

Max. Cycles at Max. Process Temperature

003

Process Temperature max. C

260

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products

- [Antennas](#)
- [Application Tooling](#)
- [Cable Assemblies](#)
- [Connected Lighting](#)
- [Connectors](#)
- [Copper Flex](#)
- [Electrical Products](#)
- [Industrial Automation](#)
- [Membrane Switches](#)
- [Optical Solutions](#)
- [Printed Electronic Solutions](#)

Quick Links

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)
- [Sitemap](#)

Resources

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback |](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Mobile Site](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshow](#)

Stay Connected



X

Molex.com would like to place cookies on your computer to help us make this website better.

To find out more about the cookies, see our [Privacy Policy](#). To accept cookies from this site, please click the 'I Accept' button.

[I Accept](#)

[I Decline](#)

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered to their respective owners.

© Copyright 2017