

Home: >

Part Number: 46436-1711

TEN60 R/A RECEPT ASSY TG-8DC-10S-7DC-TG

Image not available

Status:Active

Series:46436

Category:Molex Parts

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Series image - Reference only

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](#)

Product Environmental Compliance

EU ELV:Not Relevant

EU RoHS:Compliant

EU RoHS Phthalates:Not Contained

China RoHS:

REACH SVHC:Not Contained Per - ED/30/2017 (7 July 2017)

Low-Halogen Status:Low-Halogen

Product Compliance Statement

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

Multiple Part Industry Compliance Documents

EU RoHS, REACH SVHC, & Low-Halogen

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

▼ General

Status	Active
Category	Molex Parts
Series	46436
UPC	889056045872

▼ Physical

Net Weight	39.852/g
------------	----------

▼ Solder Process Data

Solderability Shelf Life Statement

Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

PRODUCTS

Antennas

Application Tooling

Cable Assemblies

Connected Lighting

Connectors

Copper Flex

Electrical Products

Industrial Automation

Membrane Switches

Optical Solutions

Printed Electronic Solutions

QUICK LINKS

Company Information

Contact Molex

Cross-Reference

Koch Industries

Industries

Investor Relations

Literature

Molex Racing

Press Room / Press Releases

Product Index

Sitemap

Terms & Conditions

RESOURCES

Supply Chain Transparency

Business Continuity

Compliance

ecocare

Feedback | Help

Jobs

Legal | Trademarks

Mobile Site

Supplier Portal

Privacy Policy

Tradeshows

STAY CONNECTED

C

YouTube

Twitter

f

RSS

Mobile

Envelope

in

Instagram

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017

Downloaded from [Arrow.com](#)