
**Part Number :** 2077780413
**Product Description :** Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 3 Circuits, Single Row, Glow-Wire Capable, Key D, Yellow, UL1015/UL1230 Compatible
**Series Number :** 207778
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

2077780413_sd.pdf

2077780000-PK-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

2077760000-AS-000.pdf

2077760000-PS-000.pdf

2077760000-TS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 207778 |
| Description | Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 3 Circuits, Single Row, Glow-Wire Capable, Key D, Yellow, UL1015/UL1230 Compatible |
| Application | Power, Signal, Wire-to-Wire |
| Keyword | Squba 3.6 |
| Product Name | Squba |
| UPC | 196823171604 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 3 |
| Color - Resin | Yellow |
| Flammability | 94V-0 |

Downloaded from Arrow.com.

| | |
|---|---|
| Gender | Plug |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 4.024/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.60mm |
| Pitch - Termination Interface | 3.60mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Squba 3.6 Sealed Receptacle Assembly, 3.60mm Pitch, 3 Circuits, Single Row, Glow-Wire Capable, Key D, Yellow, UL1015/ UL1230 Compatible | 2077820413 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Squba 3.6 Plug Terminal, Matte Tin Plating, UL1015/UL1230 Compatible, 20-18 AWG, Reel | 2077760003 |
| Squba Weather Cap for 6 or 3 Circuit Plug Housing | 2204230006 |



Downloaded from Arrow.com.