




TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

+ WIRE AND CABLE



HOOK UP WIRE



✓ Active



PRODUCT DRAWING
English

TE CONNECTIVITY (TE)

100G0111-1.50-45

100G0111-1.50-45

TE Internal Number: 5590673001

Alias ID: 3-1194413-8

[Always EU RoHS/ELV Compliant](#)

Cable Type **Spec 100G**

Voltage Rating (V) **600**

Wire Color **Yellow with Green Stripe**

Operating Temperature Range (°C) **-55 – 125**

Cable Style **Primary**

Product Drawings

[Customer Drawing](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Type	Spec 100G
	Cable Style	Primary
	Product Type	Wire
	Product Classification	Wire - Spec 99 & 100
Configuration Features	Number of Conductors	1
Electrical Characteristics	Voltage Rating (V)	600
Body Features	Wire Color	Yellow with Green Stripe
Dimensions	Wire Size (AWG)	15
	Wire Size (mm ²)	1.5
	Wire Diameter	2.1 mm [.0826 in]

Usage Conditions

Operating Temperature Range (°C)

-55 – 125

Other

Wire Source

United Kingdom

Product Compliance

[Statement of Compliance](#)
PDF[VIEW ALL PRODUCT COMPLIANCE](#)