



**Part Number :** [1301350268](#)  
**Product Description :** Super-Safeway Angled GFCI Outlet Box, F3 (3/4") Cord Grip Body, Including NEMA 5-20 GFCI & Duplex Receptacles with Flip Lids and 1.83m (6.0') Cord Length, 12/3 SOOW Cord & Cont. Monitor  
**Series Number :** 130135  
**Status :** Active  
**Product Category :** Power Distribution  
**Engineering Number :** 3324L123



## Documents & Resources

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance



## Part Details

### General

Status	Active
Category	Power Distribution
Series	130135
Description	Super-Safeway Angled GFCI Outlet Box, F3 (3/4") Cord Grip Body, Including NEMA 5-20 GFCI & Duplex Receptacles with Flip Lids and 1.83m (6.0') Cord Length, 12/3 SOOW Cord & Cont. Monitor
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Angled GFCI Outlet Box
UPC	78678809542

### Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	Yes
Open Neutral Relay	No
Voltage - Maximum	120V

### Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable



Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	GFCI Duplex

---

This document was generated on Sep 23, 2025