

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391002508

Status:

Active

Overview:

Eurostyle Two-Screw Barrier Strips

Description:

15.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 8 Circuits



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	Eurostyle Two-Screw Barrier Strips
Product Name	Eurostyle Two Screw
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	78172545264
Physical	
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Net Weight	62.670/g
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	10, 12, 14, 6, 8
Electrical	
Current - Maximum per Contact	63.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	M800-04-08-5-M1
Reference - Drawing Numbers	
Sales Drawing	SD-39100-017-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained per -

D(2022)9120-DC (17

Jan 2023)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION