Part Number : 936000039
Product Description : Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg11 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Part Number : 7000.6841.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg11 Thread
Cable Gland Type	IP66 - Basic
Comments	3 Gaskets: 7.50, 10.00, and 12.50mm internal diameters.
IP Rating	IP66
Product Name	Heavy-Duty Connectors
UPC	887191826110

Physical

Cable Diameter	7.00-12.00mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	14.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg11
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Enclosures Size A and B metal

Downloaded from Arrow.com.

	type

Downloaded from Arrow.com.