



Powering Business Worldwide

pe.eaton.com

Single Row Terminal Block

CB30120807CA

UPC:051712562287

Dimensions:

- **Height:** .7 IN
- **Length:** 3.48 IN
- **Width:** .7 IN

Weight:.5 LB

Warranties:

- Not Applicable

Specifications:

- **Application:** industrial
- **Mounting:** Barrier end
- **Special Features:** Break down voltage 8200V
- **Type:** Closed back
- **Voltage Rating:** 600V
- **Number Of Poles:** Eight-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #22-12 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.437 in
- **Screw Options:** Steel SEMS screw, SEMS captive screw
- **Material:** Molded thermoplastic base, nickel plated brass SEMS screw
- **Color:** Black
- **Connection:** #6-32 screw
- **Terminal Material:** Handwired

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



