

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008500105

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass Tin (Sn)



Series image - Reference only

- Documents:
- Drawing (PDF)

Product Specification PS-08-50-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	2478
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Packaging Alternative	08-50-0106 (Loose)
Product Name	KK® 396, KK® 508
UPC	800753614437
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.280/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	2478-1(P909)
Reference - Drawing Numbers	
Product Specification	PS-08-50-001
Sales Drawing	SD-2478

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2478 Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION