



Part Number : [936014686](#)
Product Description : Heavy-Duty Standard (STD)
Single Lever Bulkhead Mount Housing, Polyamide, with
1 Lever, Side Entry, with Cable Gland, Size «32x13»,
Pg16 Thread, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7908.6663.1



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66, IP67
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842653

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Diameter	8.00-14.00mm
Component Size	«32X13»
Entry Location	Side
Gland Color	Black RAL 9005
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide

Material - Housing	Polyamide
Material - Lever	Polyamide
Mounting Style	Bulkhead
Net Weight	48.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts

This document was generated on Sep 23, 2025