

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080097](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway™ Twin Tube 64W Fluorescent Work Light 12V, Cord Type 12/3 SJOOW Feed Thru 7.62m (25.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374
UL E174254

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration Non-NEMA
Outlet Feed-Through
Overview [Wide-Area Lighting Products](#)
Product Literature Order No 987650-8054
Product Name Super-Safeway™
Type Wide Area Lamps
UPC 78678867066
Woodhead Yes

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary 0.152m (6.00")
Depth 190.75mm (7.510")
Duty Industrial
Guard Included No
Guard Type N/A
Height 82.55mm (3.250")
Length 1.39m (54.620")
Material - Globe Butyrate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Adjustable Brackets
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 12/3 SOOW
Lamp Type F32/T8
Lamp Wattage - Maximum 64W
Lumens 5300
On/Off Switch No
Voltage (Fixture) - Maximum 12V AC/DC

Material Info

Old Part Number 1051-12



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
ELV Not Reviewed

Search Parts in this Series

[130108](#) Series