# 10-32 Rack Thumb Screw *TSCREW Series*







## Features

- Slotted and Phillips pan head for use with a Bladed or Phillips screw driver.
- Easily installed/removed by hand with no tools required.
- Includes factory installed, mar-resistant nylon washer.
- Heat-treated for strength.
- 10-32 x 0.625 inch length steel thumb screws.
- Black oxide finish.
- Packaged in a reusable jar.

| Part No. | Qty Included | Screw Head Diameter | Screw Head Height | Screw Length |
|---|---|---|---|---|
| **TSCREW1032-25** | 25 screws with nylon washers | 0.45 | 0.38 | 1.00 |
| **TSCREW1032-50** | 50 screws with nylon washers | 0.45 | 0.38 | 1.00 |
| **TSCREW1032-100** | 100 screws with nylon washers | 0.45 | 0.38 | 1.00 |

TAA COMPLIANT

RoHS

*Data subject to change without notice.*

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.