

# Eaton BSPMA1120S2GR

Catalog Number: BSPMA1120S2GR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, Surge arrester, Thermoplastic, UL94V12, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

## General specifications

Product Name

Eaton Bussmann series BSPM series surge arrester

Catalog Number

BSPMA1120S2GR

UPC

051712709026

Product Length/Depth

0.71 in

Product Height

3.54 in

Product Width

2.56 in

Product Weight

0.26 lb

Warranty

Five year limited warranty

Compliances

RoHS Compliant  
Contact factory

Certifications

UL 94V0  
UL Listed



## Product specifications

### Special features

Technology type MOV

### Material

Thermoplastic

### Enclosure

Thermoplastic, UL94V12

### Surge current

200 kA

### Mounting Method

35 mm DIN rail

### Nominal Discharge Current

20 kA

### Short-circuit rating

200 kA

### Type

Surge arrestor

### Operating voltage

600/1200

### Indicator type

Remote contact

### Frequency rating

50/60 Hz

### Operating temperature

-35 to 85 °C

### Application

Surge Protection

### Degree of protection

IP20

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

BSPMA1120S2GR~120V Single Phase, 1P

### Specifications and datasheets

Eaton Specification Sheet - BSPMA1120S2GR



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)