

Specification Sheet

Part Number: 126-03100

Arrowhead design makes installation quick and easy by hand.

Ties "clicks" into place upon final installation signaling installer insertion is complete.

Design provides low insertion and high extraction force.



1-Piece Cable Tie/Arrowhead Mount with Seal, 6.3" Long, 50lb Tensile, PA66HS, Green, 500/bg

Article Number 126-03100

Type T50SOSSFT6.5E-MDL

Color Green (GN)

Quantity Per bag

Product Description Arrowhead Push Ties with rubber seal secure fast and easy, while providing a special rubber seal to minimize water, dirt, or dust from getting through the mounting hole. The anchor adjusts for variations in panel thicknesses which insures a secure fixing at all times.

Short Description 1-Piece Cable Tie/Arrowhead Mount with Seal, 6.3" Long, 50lb Tensile, PA66HS, Green, 500/bg

Global Part Name T50SOSSFT6.5E-MDL-PA66HS-GN

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	6.3
Length L (Metric)	158.8
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.3
Height H (Imperial)	0.67
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.07
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	1.8
Mounting Hole Diameter D (Imperial)	0.25 - 0.26
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)