

 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Size = Standard
- A Series
- Receptacle
- Without Locking Feature
- 3 Ports

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- [RCPT. ASS'Y TRIPLE STACKED, USB, R/A, A TYPE.](#) (PDF, English)

- None Available

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version 0)
- 3D Model (IGES, Version 0)
- 3D Model (STEP, Version 0)

- Product Line Information

- Tooling

[List all Documents](#)

- Size = Standard
- Gender = Receptacle
- Number of Ports = 3
- Orientation = Right Angle
- Number of Positions = 4

- Mount Location = Top

- Panel Ground Type = Ground Finger

- Termination Method = Solder to PC Board
- Tail Length (mm [in]) = 2.85 [0.112]

- Series = A
- Locking Feature = Without
- Panel Ground = With
- PCB Retention Method = Kinked Legs
- Shell Plating = Nickel over Copper
- Pick and Place Cover = Without
- Locating Posts = Without

- Contact Termination Type = Through Hole
- Contact Mating Area Plating Material = Gold
- Contact Mating Area Plating Thickness = 30 Microinches

- Housing Color = Black

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Terminate To = Printed Circuit Board

- Panel Ground Location = Center
- Packaging Method = Tray

- Brand = AMP