
Part Number : 1300940478
Product Description : Heavy Duty Support Grip, Double Eye, Double Weave, Split Lace, Cable Diameter 88.90-101.35m (3.500-3.990"), Approximate Break Strength 5951.13kg (13120 lbs)
Series Number : 130094
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 35447



Obsolete

Documents and Resources

Drawings

PK-130227-004-001.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130094
Description	Heavy Duty Support Grip, Double Eye, Double Weave, Split Lace, Cable Diameter 88.90-101.35m (3.500-3.990"), Approximate Break Strength 5951.13kg (13120 lbs)
Product Name	Heavy Duty
Type	Support Grip
UPC	78678835447

Agency

CSA	LR32159

Physical

Approximate Break Strength	5951.13kg (13120 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	88.90-101.35mm (3.500-3.990")
Color - Grommet	N/A
Eye Type	Double
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	1.143m (45.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Obsolete

Downloaded from Arrow.com.

This document was generated on May 27, 2026

Obsolete

Downloaded from Arrow.com.