



# CH18M, Cable Tie Hanger

By Burndy  
Catalog # CH18M

Nylon Cable Hanger.



## Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

## General

Catalog Number	CH18M
Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
Trade Name	UNIRAP™
UPC	781810336656

## Dimensions

Dimension - Bundle Diameter	1.33
Max inch	
Dimension - Width inch	0.47
Dimension - Width mm	12 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	2000
Packaging Type	Bag

## Product Assets

- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Catalogs - BURNDY Master Catalog - Section G - Wire Management
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR\_CH\_CABLE\_HANGERS\_LineArt
- Sales Drawings - 50080809
- Specifications - CH18M