








- Protection level: IP 68
- Temperature range: -20°C...+80°C

Loading plan



Electrical data:
-Rated voltage: 10-30V DC
-Nominal: 2 A per Contact
-Current: 4 A per Outlet
12 A max total

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department HCS - RO	MUNTEANV	POPESCU	AVRAM	2017-04-24	Final Release	
HARTING Customised Solutions		Title har-SAB M12/8/5p M23/19p				Doc-Key / ECM-Nr.	
D-32427 Minden		Type TB	Number 090700322200			100689611/UGD/000/B	
						Rev. B	Page 1/1